

Garant**Value pack WNMG indexable insert medium machining 30 pieces HB7020-2****Order data**

Order number	GG2485 060408
GTIN	4067263093558
Item class	GGN

Technical description

Finishing/roughing assignment	Finishing
Main application	P
Tool material	Carbide
ISO code indexable insert	WNMG 060408
Cutting speed v_c main application	130 - 370 mm/min
Contents	252064 HB7020-2
Cutting depth $a_{p \min}$	0.25 mm
Corner radius	0.4 mm
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	6
Cutting depth a_p	0.3 - 4 mm

Data sheet

Cutting depth $a_{p \max}$	2.75 mm
Quantity	30
Type	HB7020-2
Cutting conditions	slightly interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2485 060408