

Garant**TCMT indexable insert for finishing 30 pieces, HB7035-2, Size: 16T308****Order data**

Order number	GG2841 16T308
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.07 - 0.25 mm/rev.
Tool material	Carbide
ISO code indexable insert	TCMT 16T308
Main application	P
Corner radius	0.8 mm
Cutting speed v_c main application	120 - 350 mm/min
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.2 - 1.5 mm
Number of changes/inserts	3
Contents	260958 HB7035-2
Cutting depth $a_{p \max}$	4 mm

Data sheet

Cutting depth $a_{p \min}$	0.55 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2841 16T308