



Wheel brush 150x0.5x6 /22.23 mm, steel-wire, twisted

- Specially developed for the professional processing of U and V-weld seams in pipeline construction, as well as for root weld seam preparation
- Edging type: twisted steel wire
- Thickness of plait: 6.0 mm

Order no.	626816000
EAN code	4007430296016
Diameter	150 mm / 6 "
Bore Ø	22.25 mm / 7/8 "
Wire thickness	0.50 mm
Maximum speed	10000 rpm
Sales unit / packaging unit	1 / 1