



Value pack abrasive flap disc long life CER conical



Order data

Order number	GG5224 60
GTIN	4067263136545
Item class	GGN

Description

Version:

- **High-quality self-sharpening ceramic grit (CER) for maximum abrasive power and low contact pressure.**
- **Active coating for cool cutting.**
- **Sturdy poly-cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.**
- **Ergonomic and vibration-damping polyester plastic backing pad (can be reset).**
- **Best results on high-power angle grinders.**

long life - very closely spaced flap strips, for **maximum tool life**.

Corresponds to 565224.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Technical description

Disc Ø	115 mm
Contents	100

Data sheet

Bore Ø	22.23 mm
Grit	60
Shape description	dished
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
abrasive, cooling coating	yes
Iron, sulphur and chlorine constituents	< 0,1 %
Product name attribute	Ø 115 mm
optimised for material	INOX
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/GG5224-60>

