

Garant**Value pack CNMG indexable insert medium machining 30 pieces HB7035-2****Order data**

Order number	GG2409 120416
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	4.25 mm
Feed f	0.2 - 0.5 mm/rev.
Corner radius	1.6 mm
ISO code indexable insert	CNMG 120416
Tool material	Carbide
Contents	250162 HB7035-2
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	1.05 mm
Number of changes/inserts	4
Main application	P
Cutting speed v_c main application	120 - 320 mm/min

Data sheet

Cutting depth a_p	0.3 - 4 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2409 120416