

Garant**SCMT indexable insert for finishing 30 pieces, HB7010-2, Size: 09T308****Order data**

Order number	GG2827 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.
Cutting speed v_c main application	120 - 350 mm/min
Finishing/roughing assignment	Finishing
Tool material	Carbide
Number of changes/inserts	4
ISO code indexable insert	SCMT 09T308
Contents	260744 HB7010-2
Cutting depth $a_{p\ max}$	3.25 mm
Corner radius	0.8 mm
Main application	P

Data sheet

Cutting depth $a_{p \min}$	0.55 mm
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2827 09T308