

**SCMT indexable insert for finishing 50 pieces, HB7010-2, Size: 120404****Order data**

Order number	GG2830 120404
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	4
Cutting depth a_p	0.2 - 1.5 mm
Feed f	0.07 - 0.25 mm/rev.
Tool material	Carbide
Cutting depth $a_{p\ min}$	0.25 mm
Contents	260748 HB7010-2
ISO code indexable insert	SCMT 120404
Main application	P
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Quantity	50

Cutting depth $a_{p \max}$	4.25 mm
Cutting speed v_c main application	150 - 500 mm/min
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2830 120404