

Garant**DCGT indexable insert for medium machining 50 pieces, HB7310, Size: 11T308****Order data**

Order number	GG3818 11T308
GTIN	4067263098140
Item class	GGN

Technical description

Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	DCGT 11T308
Feed f	0.05 - 0.5 mm/rev.
Tool material	Carbide
Cutting depth $a_{p \max}$	2.75 mm
Number of changes/inserts	2
Quantity	50
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.1 - 4 mm
Corner radius	0.8 mm

Data sheet

Main application	N
Contents	260464 HB7310
Cutting speed v_c main application	350 - 600 mm/min
Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3818 11T308