

**VBGT indexable insert for medium machining 30 pieces, HB7310, Size: 110302****Order data**

Order number	GG3828 110302
GTIN	4069515046480
Item class	GGN

Technical description

Contents	261222 HB7310
Cutting depth a_p	0.1 - 4 mm
Main application	N
Cutting speed v_c main application	350 - 600 mm/min
Cutting depth $a_{p \max}$	1.75 mm
Quantity	30
Finishing/roughing assignment	Finishing
Cutting depth $a_{p \min}$	0.15 mm
ISO code indexable insert	VBGT 110302
Feed f	0.05 - 0.5 mm/rev.
Corner radius	0.2 mm
Tool material	Carbide
Number of changes/inserts	2
Tolerance	G
Type	HB7310
Cutting conditions	continuous
Chip breaker	AM

Type of product

Indexable insert for turning

Suitable products

No Shop URL available for: GG3828 110302
