

Garant**WNMG indexable insert for roughing 50 pieces, HB7010-2, Size: 080408****Order data**

Order number	GG2495 080408
GTIN	4067263092278
Item class	GGN

Technical description

Cutting depth $a_{p \max}$	2.75 mm
Main application	P
Number of changes/inserts	6
Feed f	0.25 - 0.6 mm/rev.
Corner radius	0.8 mm
Tool material	Carbide
ISO code indexable insert	WNMG 080408
Contents	252208 HB7010-2
Cutting depth $a_{p \min}$	0.55 mm
Cutting depth a_p	1.5 - 6 mm
Finishing/roughing assignment	Roughing

Data sheet

Cutting speed v_c main application	120 - 415 mm/min
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2495 080408