

Garant**180° reverse countersinking mill, Countersink Ø D: 57mm****Order data**

Order number	217180 57
GTIN	4045197465726
Item class	210

Description**Version:****With just one cutter (z = 1).****Note:**

Dimension e = programming dimension (information on the end face). Use GARANT torque screwdriver TQ No. **211750 size 5.5** with bit No. **674252 size 20IP**.

Technical description

Shank type	Weldon
Number of cutting edges Z	1
L ₃	120 mm
Programming dimension e	9.55 mm
Countersink Ø D	57 mm
Minimum Ø d _{min}	39 mm
Shank Ø D _s h6	40 mm

Overhang L ₁	150 mm
Set of insert screws	219848 (20IP; 5.5 Nm)
suitable indexable insert	260158
Through-coolant	yes
Overall length L	220 mm
Countersink angle	180
Tool exchange	PowerCard
Type of product	Counterbores, countersinks

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/217180-57>