

Garant
CNMG indexable insert for medium machining 50 pieces, HB7010-2, Size: 120408

Order data

Order number	GG2410 120408
GTIN	4067263092278
Item class	GGN

Technical description

Contents	250158 HB7010-2
Feed f	0.2 - 0.5 mm/rev.
Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.55 mm
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	140 - 440 mm/min
Tool material	Carbide
ISO code indexable insert	CNMG 120408
Cutting depth a_p	0.3 - 4 mm
Cutting depth $a_{p \max}$	4.25 mm

Corner radius	0.8 mm
Main application	P
Quantity	50
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2410 120408