

**TCMT indexable insert for medium machining 50 pieces, HB7010-2, Size: 16T304****Order data**

Order number	GG2848 16T304
GTIN	4067263092278
Item class	GGN

Technical description

Corner radius	0.4 mm
Quantity	50
Cutting depth a_p	0.3 - 2 mm
Main application	P
Feed f	0.08 - 0.3 mm/rev.
Cutting depth $a_{p \max}$	4 mm
ISO code indexable insert	TCMT 16T304
Number of changes/inserts	3
Cutting speed v_c main application	120 - 440 mm/min
Contents	260986 HB7010-2

Data sheet

Tool material	Carbide
Cutting depth $a_{p \min}$	0.25 mm
Finishing/roughing assignment	Finishing
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2848 16T304