



BMT longitudinal toolholder, BMT: WT100



Order data

Order number	319885 WT100
GTIN	4069515004299
Item class	32U

Description

Version:

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

Suitable for conventional toolholders.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball spray nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

Mainly for external machining.

Suitable for:

CNC lathes with BMT tool turret.

- **Nakamura-Tome: NA44A, WT-100, NTJ-100, NTY³-100(V), WY-100 II/V (12 ST), SC-100, MX-100**
- **CMZ: TTS 38, 46, 52, 66 M/Y**
- **Muratec: MT 100, 1051, 1065 (15-Station)**

- **Genturn: C42MYS, CW42 MY**
- **Goodway: GTZ-1500Y**
- **Hasegawa: C25/42, CW42**

Note:

Other BMT holders with different sizes and dimensions are available on request.
Please note that you must check the compatibility of the holder with your machine before purchasing. We cannot guarantee that it will fit correctly.

Technical description

h_2	80 mm
L_2	55 mm
b_2	52 mm
h_1	20 mm
L_1	40 mm
x	62 mm
Type of product	Steel toolholder