

**Value pack CNMG indexable insert medium machining 30 pieces HB7010-2****Order data**

Order number	GG2407 09T308
GTIN	4067263092278
Item class	GGN

Technical description

Number of changes/inserts	4
Cutting depth $a_{p \min}$	0.55 mm
ISO code indexable insert	CNMG 09T308
Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.3 - 4 mm
Cutting depth $a_{p \max}$	3.25 mm
Cutting speed v_c main application	140 - 440 mm/min
Finishing/roughing assignment	Finishing
Contents	250152 HB7010-2
Tool material	Carbide
Main application	P

Data sheet

Corner radius	0.8 mm
Quantity	30
Type	HB7010-2
Cutting conditions	continuous
Chip breaker	SM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2407 09T308