

**TCMT indexable insert for finishing 30 pieces, HB7035-2, Size: 110202****Order data**

Order number	GG2841 110202
GTIN	4067263092278
Item class	GGN

Technical description

Main application	P
Cutting speed v_c main application	120 - 350 mm/min
Cutting depth $a_{p \max}$	2.75 mm
Cutting depth $a_{p \min}$	0.25 mm
Feed f	0.07 - 0.25 mm/rev.
Contents	260950 HB7035-2
Corner radius	0.4 mm
ISO code indexable insert	TCMT 110202
Number of changes/inserts	3
Finishing/roughing assignment	Finishing
Tool material	Carbide

Cutting depth a_p	0.2 - 1.5 mm
Quantity	30
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SS
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2841 110202