

**CCMT indexable insert for medium machining 50 pieces, HB7130-2, Size: 060204****Order data**

Order number	GG3510 060204
GTIN	4067263096122
Item class	GGN

Technical description

Cutting depth a_p	0.2 - 4 mm
Feed f	0.1 - 0.4 mm/rev.
Main application	M
Quantity	50
Tolerance	M
Tool material	Carbide
Cutting depth $a_{p \min}$	0.25 mm
Contents	260142 HB7130-2
Cutting depth $a_{p \max}$	2 mm
Corner radius	0.4 mm

Data sheet

Cutting speed v_c main application	70 - 240 mm/min
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
ISO code indexable insert	CCMT 060204
Type	HB7130-2
Cutting conditions	slightly interrupted
Chip breaker	VM
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG3510 060204