

Garant**DNMG indexable insert for roughing 50 pieces, HB7035-2, Size: 150612****Order data**

Order number	GG2437 150612
GTIN	4067263092278
Item class	GGN

Technical description

Feed f	0.25 - 0.6 mm/rev.
Cutting depth $a_{p \min}$	0.8 mm
Corner radius	1.2 mm
ISO code indexable insert	DNMG 150612
Cutting depth a_p	1.5 - 6 mm
Main application	P
Cutting depth $a_{p \max}$	3.75 mm
Cutting speed v_c main application	100 - 290 mm/min
Finishing/roughing assignment	Roughing
Contents	250864 HB7035-2
Tool material	Carbide

Data sheet

Number of changes/inserts	4
Quantity	50
Type	HB7035-2
Cutting conditions	heavily interrupted
Chip breaker	SG
Type of product	Indexable insert for turning

Suitable products

No Shop URL available for: GG2437 150612